




UNIT: mm



CABLE BLACK PRINT
USB CABLE E189529  AWM 2725 28AWG/1PR AND
24AWG/2C 80°C 30V VW-1

PIN ASSIGNMENT:



IPC/PE BAG

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V

⑥	PE BAG	1/10	CLEAR SIZE:230*300*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS".
⑤	PE BAG	1	CLEAR SIZE:100*200*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
④	TIE	1	WHITE L=100mm
③	OUT JACKET	12g	BEIGE(V-29#) PVC-40P (MOULD NO:WM-65)
②	CABLE	1	BEIGE(V-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm L=1000±10MM
①	CONN	2	USB2.0 B MALE NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE
NO.	NAME	Q'TY	

SPECIFICATION

CNC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWED	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1040-BE-00100
DECIDED		DATE	2012-02-16
VERSIONS/EDITION	A/0	PROJECTION	