




FEATURES:

- Converts WE310 (PJ-051) Female into Alligator clips.
- Available in three lengths
- Length other than those specified are available on request.

MATERIALS:

Conn: 1st End – PJ-051 Phone Plug

Material: Body – Brass

Handle – Nylon. Color: Red.

Cable:

2 Cond. Twisted Pair – 18 AWG stranding

65 X 36 t.c., Vinyl insulation.

Marking “POMONA 3352-A-*”. Color: Gray

Breakout: PVC molded to breakout leads and cable.

Color matches color of cable.

Breakout Leads:

20 AWG stranding 41 X 36 t.c., PVC insulated, 2.21 (.087) O.D. Color matches color of insulator.

Conn: 2nd End – Insulated Alligator Clips

Material: Steel

Finish: Nickel plated. Insulation: Vinyl.

Color: Black and red.

RATINGS:

Operating Temperature: +50° C. (+122° F.) Max.

Operating Voltage: 150V RMS/DC

Current: 5 Amperes


ORDERING INFORMATION: Model 3352-A-XX XX=Cable Length, Standard Lengths: 36(914), 60(1524), 84(2134), 120(3048)

Ordering Example: 3352-A-84” (2134)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA



FEATURES:

- Shielded cable to reduce noise
- Provides quick access from WE-310 jack to terminals
- Available in three lengths
- WE-310 Plug molded to the cable to provide optimum durability

MATERIALS:

Plug – Nickel plated brass

Cable – 2 Conductor shielded twisted pair, PVC jacket and insulation

Breakout – Molded

Alligator – Nickel plated steel, Insulator - vinyl

RATINGS:

Operating Voltage – 150 VRMS

Operating Temperature - 122°F (50°C)

ORDERING INFORMATION: Model 3352N-A-XX

XX = Cable Length, Standard Lengths: 36" (914 mm), 60" (1524 mm), 84" (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA