



Datasheet for part number VIP08Y2

Our Descriptive Part Number: VIP08Y2
Our Global Manufacturing Part Number: 000L05010
Brand: VEAM Product Category: Circular Product Line: Veam CIR, VBN, Other Series: CIR / FRCIR

Product Datasheet	
SERIES	Line Drain (female contact)
SHELL STYLE	Elbow Plug
LABLE COLOR	Blue
CONTACT TYPE	700 A threaded post
MAXIMUM CURRENT RATING	700 A
CABLE GLAND	Not included - M50 thread. Use plastic material
MAXIMUM RATED VOLTAGE TO EARTH	1,5K Vac / 2K Vdc
MINIMUM FLASHOVER	9K Vdc or Ac peak
OPERATING TEMPERATURE RANGE	-40°/+100°
INSULATION RESISTANCE	up to 5000 Mohms
INGRESS PROTECTION (MATED)	IP67
PROTECTION AGAINST ELECTRICAL SHOCK	IP2X
FLAMMABILITY	UNI 11170 Compliant (I2F2 grade)
CONTACT RETENTION	Mechanical
MATING METHOD	Double start thread
MATING CYCLES	500
OPERATING VOLTAGE	1,5K Vac / 2K Vdc
SHELL MATERIAL FINISH	Thermoplastic
CABLE RANGE	up to 240 sqmm
KEYS ORIENTATION	120°