



Precision Tweezers

We Offer a Wide Variety of Tweezers To Meet a Broad Range Of Applications and 2 Different Quality Grades.

In order to choose the best tool for your application:

1. Determine the type of points best suited for your application.
2. Refer to the material guide below and select the correct material for your application.
3. Determine the quality level required for your application if applicable. (Table 1)
4. Remember there is a trade-off between hardness, magnetism and corrosion resistance. (Table 2)

QUALITY GRADES (Table 1)

Brand Recommend For:

Accu-Tek
★★★★ Made from the finest steels. Perfectly balanced for a superior feel. Light weight with soft tension with accurately finished points. Recommended for work under high power magnification aerospace and micro electronics and in applications where high precision is required. All Accu-Tek precision tweezers are made from anti-acid, anti-magnetic stainless steel.

Technik
★★★ Finely crafted tweezers. Anti-glare finish to reduce eye strain. Hand finished points for accuracy. Recommended for micro electronics and precision assembly.

MATERIAL SELECTION GUIDE (Table 2)

Material	Tip Hardness	Magnetism	Corrosion Resistance
Carbon Steel	Excellent	Yes	Low
Stainless Steel	Very Good	Some	Good
Stainless Steel, Anti-magnetic, Anti-acid	Good	None to very little	Excellent, Resists Acids
Carbon Composite	Soft	None	Non Corrosive

Ceramic ESD Safe, non magnetic. Resists all chemicals except hydrofluoric acids. Withstands temperatures up to 900°F. Heat sink fighter. For more details on the features of our ceramic tweezers please refer to page 93.

Plastic We offer static dissipative plastic tweezers. Plastic tweezers are non magnetic, resist virtually all commercial solvents. Non absorbent and easy to clean. Tips are non-marring.

Carpenter 20, Nickel, Titanium, Beryllium, Copper & Brass: Available on special order.

SPECIAL COATINGS (Available on non magnetic steel only)

TE - Teflon Superior anti-scratch, non-stick material. Acid resistant. 400°F/200°C
EP - Epoxy Good electrical insulation and resistance to chemicals. Antiglare. 300°F/150°C
RY - Ryton Very smooth. Excellent resistance to chemicals and temperature.
PY - Pyron Water and solder repellent. Non conductive 950°F/500°C
GP - Gold Plating Very high corrosion resistance. Smooth anti-scratch, anti-glare, no tarnish finish.

* To order tweezers with above mentioned coatings, please add the symbol to the order #.

* Call AVEN for price and delivery time.