

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130107-0030](#)
Status: **Active**
Description: Super-Safeway™ Assembled Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead with Guard 3.04m (10.0'), Overall Length 30.48m (100.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130107
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Product Literature Order No	987650-8055
Product Name	Super-Safeway™
Type	String Lights
UPC	78678879626
Woodhead	Yes

Physical

Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	N/A
Depth	46.48mm (1.830")
Duty	Industrial
Guard Included	362
Guard Type	N/A
Height	101.60mm (4.000")
Length	30.48m (100.0')
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Assembled

Electrical

Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number 310123



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130107Series](#)