

TradeMaster® & Specification Grade GFCI Receptacles

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC

Pass & Seymour




GFCIs

Features


- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

Specifications


- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity



1595-W



2095-W



1595-SW



NEMA 5-15R



NEMA 5-20R

Available in Bulk Packaging, i.e. 1595-W20 is 20 pack, 1595-W100 is 100 pack. Please contact Customer Support at 1-800-223-4189.

Catalog Number	Rating A. VAC		Color	NEMA Config. No.	3rd Party Compliance		
					 UL943 C22.2 No. 144	 UL498 C22.2 No. 42	FSUL WC596
TradeMaster®/Spec Grade 15 Amp Duplex GFCI							
1595-I	15	125	Ivory	5-15R	•	•	•
1595-W	15	125	White	5-15R	•	•	•
1595	15	125	Brown	5-15R	•	•	•
1595-GRY	15	125	Gray	5-15R	•	•	•
1595-BK	15	125	Black	5-15R	•	•	•
1595-RED	15	125	Red	5-15R	•	•	•
1595-LA	15	125	Light Almond	5-15R	•	•	•
TradeMaster®/Spec Grade 15 Amp Duplex GFCI with Auto-Ground							
1595-SI	15	125	Ivory	5-15R	•	•	•
1595-SW	15	125	White	5-15R	•	•	•
1595-SLA	15	125	Light Almond	5-15R	•	•	•
Specification Grade 20 Amp Duplex GFCI							
2095-I	20	125	Ivory	5-20R	•	•	•
2095-W	20	125	White	5-20R	•	•	•
2095	20	125	Brown	5-20R	•	•	•
2095-GRY	20	125	Gray	5-20R	•	•	•
2095-BK	20	125	Black	5-20R	•	•	•
2095-RED	20	125	Red	5-20R	•	•	•
2095-LA	20	125	Light Almond	5-20R	•	•	•
Specification Grade 20 Amp Duplex GFCI with Auto-Ground							
2095-SI	20	125	Ivory	5-20R	•	•	•
2095-SW	20	125	White	5-20R	•	•	•
2095-SLA	20	125	Light Almond	5-20R	•	•	•

Available Spring 2006.

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.

TradeMaster® & Spec. Grade GFCI Receptacles