

Panel Printer
AP1200



AP1200: H=67, W=115, D=104mm
AP1200-12V: D=112mm

- Compact and stylish
- Easy paper-load system
- High speed and high quality fixed head thermal mechanism
- 5V or 12V versions available
- Ideal for data recording applications
- Strong polycarbonate case

Specification	AP1200	AP1200-12V
Print Method	Fixed head thermal	
Number of columns	32 (default), 24 or 42	
Print Speed	13 lines/sec (default character size)	50mm/second
Paper Width (mm)	57.5 ± 0.5	
Dots per line	384 (8dots/mm)	
Power Supply	5V to 8.5Vdc	12V ± 10%
Weight (including paper)	315g	390g

419115

Mftrs. List No.	Order Code	Price Each
AP1200	109-5840 ●	
AP1200-12V	109-5841 ●	
Paper Roll, 22m	109-5842	