

1807A Coax - High-Flex S-Video Cable

For more Information
please call

1-800-Belden1

**General Description:**

30 AWG stranded (7x38) .012" tinned copper conductors, foam HDPE insulation, tinned copper serve shield (90% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
2	30	7x38	TC - Tinned Copper	0.3302

Total Number of Conductors: 2

Insulation**Insulation Material:**

Insulation Material
FHDPE - Foam High Density Polyethylene

Inner Shield**Inner Shield Material:**

Type	Inner Shield Material	Coverage (%)
Spiral Serve (each coax)	TC - Tinned Copper	90

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 2.794 x 5.842 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 20.835 Kg/Km

Max. Recommended Pulling Tension: 52.044 N

Min. Bend Radius/Minor Axis: 25.400 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

1807A Coax - High-Flex S-Video Cable

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Plenum Number:	7700A
----------------	-------

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

56.7613

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

328.1

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)

24.6075

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
-------------	-----------------------

1	1.9686
---	--------

5	4.5934
---	--------

10	6.8901
----	--------

30	12.4678
----	---------

50	16.7331
----	---------

100	24.9356
-----	---------

200	37.0753
-----	---------

400	55.4489
-----	---------

700	76.4473
-----	---------

900	88.2589
-----	---------

1000	93.8366
------	---------

Max. Operating Voltage - Non-UL:

Voltage

300 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1807A B59U1000	305 MT	6.804 KG	BLACK, MATTE	C	2 #30 FHDPE SRV PVC DUAL
1807A B59U500	152 MT	3.629 KG	BLACK, MATTE		2 #30 FHDPE SRV PVC DUAL
1807A B591000	305 MT	6.804 KG	BLACK, MATTE	C	2 #30 FHDPE SRV PVC DUAL
1807A B59500	152 MT	3.402 KG	BLACK, MATTE		2 #30 FHDPE SRV PVC DUAL

Notes:

1807A Coax - High-Flex S-Video Cable

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 04-11-2008

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.