

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
E	B		A	EBD0-0035-03		18FEB04	FWK

- NOTES:
- 1

SINGLE PACK IN ACCORDANCE WITH SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH SPEC 107-3275
- 3

0.08μm Au PLATING OVER 1.27μm Ni PLATING
- 4

0.08μm Au PLATING OVER 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
- 5

0.76μm Au PLATING OVER 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
- 6

PASSIVATED
- 7

WHITE BRONZE PLATING
- 8


PLATING AS PER BODY, EXCEPT FOR PASSIVATED WHICH IS NICKEL PLATED
- 9

HAND TOOL 9-1478240-0
- 10


DIE SET 9-1478242-0
- 11

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 12


ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED
CRIMP SLEEVE
A/F HEX



RECOMMENDED
CABLE STRIPPING DIM'S



1	1	1	1	1	1	1	1	BRASS		CRIMP SLEEVE	7
1	1	1	1	1	1	1	1	BRASS		CENTER CONTACT	6
1	1	—	—	—	—	—	—	BRASS		BODY	5
—	—	1	1	—	—	—	—	BRASS		BODY	5
—	—	—	—	1	1	—	—	STAINLESS STEEL		BODY	5
—	—	—	—	—	—	1	1	STAINLESS STEEL		BODY	5
1	1	1	1	1	1	1	1	STAINLESS STEEL		CIRCLIP	4
1	1	1	1	1	1	1	1	SILICON		GASKET	3
1	1	1	1	1	1	1	1	PTFE		INSULATOR	2
1	1	—	—	—	—	—	—	BRASS		SHELL	1
—	—	1	1	—	—	—	—	BRASS		SHELL	1
—	—	—	—	1	1	—	—	STAINLESS STEEL		SHELL	1
—	—	—	—	—	—	1	1	STAINLESS STEEL		SHELL	1
4--1	4--0	3--1	3--0	2--1	2--0	1--1	1--0	MATERIAL		DESCRIPTION	ITEM
											
QUANTITY PER ASSY								PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN R.SMITH 18FEB04

CHK S.PARLOW 18FEB04

APVD F.WHEELER-KING 18FEB04

PRODUCT SPEC 108-3460

APPLICATION SPEC 411-3276

WEIGHT -

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
SMA STRAIGHT PLUG NON CAPTIVE SOLDER CONTACT
CRIMP ATTACHMENT
RG58C/U, 141A/U, URM43, URM76, KX15

SIZE A3 CAGE CODE 00779 DRAWING NO C-1478915

RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 1 REV A