





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/29/10	

APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PANEL CUT-OUT
(THICKNESS 2.0mm Max)

SPECIFICATIONS:

Material:

Insulator: PC, rated UL498 5-15R

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 125 VAC

Current rating: UL & CSA: 15 Amps max.

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES	HILES		
.X ± .10	ØX ± .10		
.XX ± .020	ØXX ± .015		
.XXX ± .015	ØXXX ± .010		
APPROVALS		DATE	
DRAWN	DY	6/29/10	
CHECKED			
APPROVED			

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

NEMA RECEPTACLE

TITLE

NEMA RECEPTACLE

SIZE

PART NO.

NEMA-5-2-A

REV.

-

REF:

S00061T

SCALE: NTS

SHEET 1 OF 1