

CONTACT LAY-OUT

ROW Z,F : MATING LEVEL 3 / REAR MATING LEVEL 3
ALL POS


ROW A,B,E : MATING LEVEL 2 / REAR MATING LEVEL 3
ALL POS

ROW C : MATING LEVEL 2 / REAR MATING LEVEL 3
ALL POS EXCEPT POS 10: MATING LEVEL 3

ROW D : MATING LEVEL 2 / REAR MATING LEVEL 3
ALL POS EXCEPT POS 11: MATING LEVEL 1

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS TERUGZENDING VERPLICHT.





PERFORMANCE CHARACTERISTICS

CURRENT RATING : 1,5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
RATED VOLTAGE : 500 V AC (CONT / CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE : 20 mΩ MAX
INSERTION FORCE : 0.75 N MAX / CONT
EXTRACTION FORCE : 0.15 N MIN / CONT
INSULATION RESISTANCE : 10⁴ MΩ MIN

NOTES

- "--" PERFORMANCE LEVEL INDICATION: Z1= PL3 (SHORT) GC= PL3 (REAR PLUG-UP)
(SEE CAT.NR.) N9= PL2 GF= PL2
E9= PL1 GL= PL1
- THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
- MEASURED AT THE BOTTOM.

MALE SIGNAL STRAIGHT PRESS-FIT-TO-BOARD CONNECTOR						
WITHOUT SERVICECENTER						
1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	MILLIPACS 2 / TYPE A / SHIELDED		
	DRAFT	17-11-95	W.Panis	CAT. No. HM2P07PNG1A4--		
	CHECKED			<div><div></div><div>FCI MECHELEN N.V. A. SPINOYSTRAT 8, 2800 MECHELEN</div></div>		
	PROD. MGR.					
	PR. ENG. MGR.					
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PR. MGT. MGR.			SCALE		3 / 1
ALL DIMENSIONS IN MM	REFERENCES / REFERENTIES			BS,C , 201632, 019		
 ALLE AFMETINGEN IN MM				DRAWING No. CUSTOMER DRAWING		REVISION A

