

D

D

C


C

B

B

A

A



- 1 BERYLLIUM COPPER PER ASTM-B-197 OR ASTM-B-643.
- 2 BRASS PER ASTM-B-16.
- 3 PTFE PER ASTM-D-1710.
- 4 GOLD PLATE PER ASTM-B-488, TYPE 2, GRADE C, .000050 [0.00127] MIN THK OVER NICKEL PLATE PER QQ-N-290, .000050 [0.00127] MIN THK.
- 5 THIS AREA SOLDER COATED WITH SN60 OR SN63 SOLDER. (1663535-2 ONLY)

.026 [0.66] MAX	.047 [1.19] MAX	5	1663535-2
.020±.002 [0.51±0.05]	.040±.002 [1.02±0.05]	-	1663535-1
DIM B	DIM A	SOLDER DIP	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 3-24-04	tyco Electronics		TYCO Electronics Harrisburg, PA 17105-3608
DIMENSIONS: INCHES [mm]		CHK S.GLATFELTER 3-24-04	NAME		
		APVD S.GLATFELTER 3-24-04	PIN CONTACT ASSY, COAX, SIZE 5, REAR RELEASE, POSTED, ARINC 600		
		PRODUCT SPEC	SIZE		
		APPLICATION SPEC	CAGE CODE		
MATERIAL		FINISH	DRAWING NO		RESTRICTED TO
SEE CALLOUTS		SEE CALLOUTS	A2 00779 C- 1663535		-
CUSTOMER DRAWING			SCALE	SHEET	REV
			8:1	1 OF 1	0