




Heyco® Nylon Locknuts

NPT Thread

**EXPANDED
PRODUCT
RANGE**


THREAD TYPE AND SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Black	Gray		A		B	
				Thickness		Wrenching Flats	
				in.	mm.	in.	mm.
1/4 NPT	M9142	M9143	NLN 1/4 NPT	.265	6,7	.748	19,0
3/8 NPT	8461	8462	NLN 3/8 NPT	.265	6,7	1.058	26,9
1/2 NPT	8463	8464	NLN 1/2 NPT	.265	6,7	1.058	26,9
3/4 NPT	8465	8466	NLN 3/4 NPT	.265	6,7	1.312	33,3
1 NPT	8467	8468	NLN 1 NPT	.256	6,7	1.605	40,8
1-1/4 NPT	M9144	M9145	NLN 1-1/4 NPT	.281	7,1	1.968	50,0
1-1/2 NPT	M9150	M9151	NLN 1-1/2 NPT	.32	8,1	2.75	69,9
2 NPT	M9156	M9157	NLN 2 NPT	.38	9,5	2.85	72,4

Standard Colors: Black or Gray.

PG Thread

THREAD TYPE AND SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Black	Gray		A		B	
				Thickness		Wrenching Flats	
				in.	mm.	in.	mm.
PG 7	3165	3166	NLN PG 7	.218	5,5	.750	19,1
PG 9	3167	3168	NLN PG 9	.218	5,5	.859	21,8
PG11	3169	3170	NLN PG 11	.218	5,5	.937	23,8
PG 13.5	3171	3172	NLN PG 13.5	.250	6,4	1.062	27,0
PG 16	3173	3174	NLN PG 16	.250	6,4	1.171	29,7
PG 21	3175	3176	NLN PG 21	.281	7,1	1.406	35,7
PG 29	3177	3178	NLN PG 29	.281	7,1	1.812	46,0
PG 36	M9146	M9147	NLN PG36	.281	7,1	2.244	56,9
PG 42	M9152	M9153	NLN PG42	.32	8,1	2.75	69,9
PG 48	M9158	M9159	NLN PG48	.38	9,5	2.85	72,4

Standard Colors: Black or Gray.

Metric Thread

THREAD TYPE AND SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Black	Gray		A		B	
				Thickness		Wrenching Flats	
				in.	mm.	in.	mm.
M12	M9130	M9131	NLN M12	.218	5,5	.750	19,1
M16	M9132	M9133	NLN M16	.218	5,5	.870	22,1
M20	M9134	M9135	NLN M20	.245	6,2	1.062	27,0
M25	M9136	M9137	NLN M25	.278	7,1	1.378	35,0
M32	M9138	M9139	NLN M32	.281	7,1	1.614	41,0
M40	M9140	M9141	NLN M40	.281	7,1	1.968	50,0
M 50	M9148	M9149	NLN M50	.32	8,1	2.75	69,9
M 63	M9154	M9155	NLN M63	.38	9,5	2.85	72,4

Standard Colors: Black or Gray.

Quick Specs

Material	Polyamide 6/6 "Nylon"
Flammability Rating	94V-2 Standard—Consult factory for VO material
Material Temperature Index	125°C—Maximum temperature on the part shall not exceed 105°C