

[HOME](#) • [CHECK ORDER](#) • [ABOUT US](#) • [CONTACT US](#) • [REQUEST CATALOG](#)*Innovations Since 1908***PRODUCT FAMILIES**[Pin Headers](#)[and Sockets](#)[Clips and Insulators](#)[Banana Plugs and Jacks](#)[Grabbers, Probes and Spade Terminals](#)[Test Leads and Patch Cords](#)[Coaxial Cable Assemblies](#)[Coaxial Test Leads](#)[Coaxial Break-Outs](#)[DMM Kits](#)**ISO 9001:2000**

Coaxial Break-Outs

Mini-Micro-Plunger to BNC Male



Model# BU-1450-C-**-0

- Material: BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body; Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm; Plunger: nylon housing, stainless steel spring and beryllium copper contact
- **Length: - 12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor

CHECK INVENTORY**Insulated Alligator Clips to BNC Male With RG58**



Model# BU-5030-C-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body (RG174/U BNC is a commercial connector with nickel-plated body); Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm
- **Length: - 12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor

CHECK INVENTORY

BNC Male Breakout to Tinned End Wires



Model# BU-5100-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS on center conductor

CHECK INVENTORY

BNC Male Breakout to Mini-Micro-Grabbers



Model# BU-5114-A-4-0

- Material: BNC Male Connector: quality tarnishresistant, plated brass with a gold-plated brass center contact, ABS housing; Mini-Micro-Grabbers (No.208) conductor and abrasion resistant, nylon housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 150 VRMS, 5 Amp

CHECK INVENTORY

Insulated BNC Male to BNC Female




polyethylene dielectric; Coaxial Cable: RG58, 50 ohm

- **Length: - 12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 500 VRMS on center conductor

[CHECK INVENTORY](#)

BNC Male Breakout to Stackable Single Banana Plugs



Model# BU-5120-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Banana Plug: premium nine-leaf, nickel-plated beryllium copper springs and copper alloy 360 bodies for minimum stacked in multiples, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amp

[CHECK INVENTORY](#)

BNC Male Breakout to Insulated Mini-Alligator Clips



- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Clip: Mueller No. 30BL with No. 31 insulators; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 10 Amp

[CHECK INVENTORY](#)

BNC Male Breakout to Stackable 0.080" (2.0mm) Pin Plugs



Model# BU-5144-A-4-0

- Material: BNC Male Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Pin Tip: nickel-plated brass 0.080" (2.0mm) dia; 0.500" (12.7mm) long; Tip Jack: Accepts 0.080" (2.0mm) dia. pin, nickel-plated, alloy 360 copper body; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

[CHECK INVENTORY](#)

BNC Female Breakout Style to Tinned End Wires



Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation

- Rating: Hands free testing at 300 VRMS, 5 Amps

[CHECK INVENTORY](#)

BNC Female Breakout to Mini-Micro-Grabbers




Model# BU-5214-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Mini-Micro-Grabbers (No.208): conductor and abrasion resistant, nylon housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

[CHECK INVENTORY](#)

BNC Female Breakout to Stackable Single Banana Plugs



Model# BU-5220-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Banana Plug: premium nine-leaf, nickel-plated beryllium copper springs and copper alloy 360 bodies for minimum stacked in multiples, ABS housing; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 10 Amps

[CHECK INVENTORY](#)

BNC Female Breakout to Insulated Mini-Alligator Clips



Model# BU-5231-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Clip: Mueller No. 30BL with No. 31 insulators; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

CHECK INVENTORY

BNC Female Breakout to Stackable 0.080" (2.0mm) Pin Plugs



Model# BU-5244-A-4-0

- Material: BNC Female Connector: quality tarnish-resistant, plated brass with a gold-plated brass center contact, ABS housing; Pin Tip: nickel-plated brass 0.080" (2.0mm) dia; 0.500" (12.7mm) long; Tip Jack: accepts 0.080" (2.0mm) dia. pin, nickel-plated, alloy 360 copper body; Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation
- Rating: Hands free testing at 300 VRMS, 5 Amps

CHECK INVENTORY

Insulated Alligator Clips to BNC Male With RG174



Model# BU-5330-F-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; BNC Male Connector: MIL-C-39012, gold-plated center contact and silver-plated body (RG174/U BNC is a commercial connector with nickel-plated body); Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS on center conductor

CHECK INVENTORY

TOOL SEARCH TOOLS

MUELLER OR DISTY STK SEARCH /
PRODUCT DATA

PART #

SEARCH

TOOL

CROSS COMPETITOR PART #

Choose a Brand

PART #

SEARCH

TOOL

**MeterMate® DMM ACCESSORY
SELECTOR**

Select Meter Make

Select a Make First

TOOL

**BUILD A PCB HEADER OR
SOCKET**

OVER 10,000 IN STOCK!

GO

© 2008 Mueller Electric Company, Inc.

[Home](#) | [Products](#) | [Check Order Status](#) | [About Us](#) | [Contact Us](#) | [Request a Catalog](#) | [Site Map](#)