




Description:

Hour meters HK-46 are designed for the determination and monitoring of operating time, warranty period and maintenance intervals on electrically driven machines and devices, mainly in mechanical processing, woodworking, textile and paper industry, on central heating boilers, electrical furnaces, power drives and rectifiers etc. They are available in a variety of mounting techniques, for all common voltages and with a mounting depth of only 32mm. As a special version, they offer a fully sealed plastic housing. Hour meters are connected in parallel to the control circuit behind the start gear, thus working only during the operation of a machine or device. The hour meters cover a time range from 0 to 99,999.99 h (AC) resp. 999,999.9 (DC). They restart automatically at 0 when leaving the range limit. There is no separate reset facility.


Technical Data	AC	DC
Connection: Combined -Simple	Flat Pins 6.3 × 0.8mm with Screw Terminals Flat Pins 6.3 × 0.8mm	Flat Pins 6.3 × 0.8mm with Screw Terminals Flat Pins 6.3 × 0.8mm
Supply Voltage	25V, 48V, 60V, 110V, 230V, (± 10%)	6 – 30V, 10 – 80V, 110V (± 10%)
Mains Frequency	50Hz, 60Hz	-
Motor	Synchronous Motor	Step Motor
Protection Class	IP 40 front side	IP 40 front side
Operating Temp. Range	-25°C to +80°C	-20°C to +70°C
Reading Accuracy	1/100 hour (36 sec.)	1/10 hour (6min.)
Counting Range	99,999.99 hours	99,999.99 hours
Number of Digits	5 Integers, 2 Decimals	6 Integers, 1 Decimal
Digit Size	4mm	4mm
Digit Colour	Integers: White Decimals: Red	Integers: White Decimals: Red
Housing Colour	Black	Black
Mounting	Fork Clamp G, Snap Fastener F, DIN Rail D, Aluminium Clamp A	Fork Clamp G, Snap Fastener F, DIN Rail D, Aluminium Clamp A
Front Dimensions	48 × 48mm, 72 × 72mm	55 × 55mm, 72 × 72mm
Special Version	IP 65	IP 65

Hour Counter

Mounting Hole




Mounting A




x (mm)	y (mm)	Mounting Hole
48 × 48	6	1
55 × 55	7	1, 2 or 3
72 × 72	7	1, 2 or 3

Mounting D



Mounting F




x (mm)	y (mm)	Mounting Hole
48 × 48	6	1

Dimensions : Millimetres

Hour Counter



Mounting G



Dimensions : Millimetres

x (mm)	y (mm)	Mounting Hole
48 × 48	6	1
55 × 55	7	1, 2 or 3
72 × 72	7	1, 2 or 3

Part Number Table

Description	Part Number
Hour Counter, Elect-Mech	HK4624VAC
	HK46110VAC
	HK46240VAC
Bezel, 55 × 55	HK4655X55
Bezel, 72 × 72	HK4672X72

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicom is the registered trademark of the Group. © Premier Farnell plc 2012.