


PCI-1735U PCI-1737U PCI-1739U

64-ch Digital I/O and Counter
Universal PCI Card

24-ch Digital I/O Universal PCI Card

48-ch Digital I/O Universal PCI Card



Features

- ISA-Compatible with PCL-720+ (PCI-1735U), PCL-724 (PCI-1737U) and PCL-731 (PCI-1739U)
- TTL-level digital input and output compatibility
- Emulates mode 0 of 8255 PPI (PCI-1737U and PCI-1739U)
- Interrupt handling capability (PCI-1737U and PCI-1739U)
- Output status readback (PCI-1737U and PCI-1739U)
- 3 programmable counter/timer channels and User configurable clock source (PCI-1735U)
- Breadboard area for custom circuits (PCI-1735U and PCI-1739U)
- PCI universal card

Specifications

Digital Input

- **Channels** PCI-1735U: 32
PCI-1737U: 24 (shared with output)
PCI-1739U: 48 (shared with output)
- **Compatibility** 5 V/TTL
- **Input Voltage** Logic 0: 0.8 V max.
Logic 1: 2.0 V min.
- **Interrupt Capable Ch.** PCI-1737U: 1
PCI-1739U: 2

Digital Output

- **Channels** PCI-1735U: 32
PCI-1737U: 24 (shared with input)
PCI-1739U: 48 (shared with input)
- **Compatibility** 5 V/TTL
- **Output Voltage** PCI-1735U: Logic 0: 0.5 V max.
Logic 1: 2.0 V min.
PCI-1737U/1739U: Logic 0: 0.4 V max.
Logic 1: 2.4 V min.
- **Output Capability** PCI-1735U: Sink: 0.5 V max @ 24 mA
Source: 2.0 V min. @ 15 mA
PCI-1737U/1739U: Sink: 0.4 V max. @ 24 mA
Source: 2.4 V min. @ 15 mA

Counter/Timer (PCI-1735U)

- **Channels** 3
- **Resolution** 16 bits
- **Compatibility** 5 V/TTL
- **Max. Input Frequency** 1 MHz
- **Re. Clock Internal** Selectable 1 MHz, 100 kHz, or 10 kHz base clock
- **Ext. Clock Frequency** Jumper selectable divider: x2, x1, x0.5, and x0.25
- **Prog. Counter Modes** 6

General

- **Bus Type** Universal PCI V2.2
- **I/O Connectors** PCI-1735U: 5 x 20-pin box header
PCI-1737U: 2 x 20-pin & 1 x 50-pin box header
PCI-1739U: 2 x 50-pin box header
- **Dimensions (L x H)** 175 x 100 mm (6.9" x 3.9")
- **Power Consumption** PCI-1735U: 5 V @ 98.8 mA (max.)
PCI-1737U: 5 V @ 294.9 mA (max.)
PCI-1739U: 5 V @ 540.8 mA (max.)
- **Operating Temperature** 0 ~ 65° C (32 ~ 149° F)
- **Storage Temperature** -25 ~ 80° C (-13 ~ 176° F)
- **Storage Humidity** 5 ~ 95% RH, non-condensing (refer to IEC 68-2-3)

Ordering Information

- **PCI-1735U** 64-ch Digital I/O and Counter Card
- **PCI-1737U** 24-ch Digital I/O Universal PCI Card
- **PCI-1739U** 48-ch Digital I/O Universal PCI Card

Accessories

- **PCL-10120-1** IDC-20 Flat Cable, 1 m
- **PCL-10120-2** IDC-20 Flat Cable, 2 m
- **PCL-10150-1.2** 50-pin Flat Cable, 1.2 m
- **ADAM-3920** 20-Pin Flat Cable Terminal, DIN-rail Mount
- **ADAM-3950** 50-pin DIN-rail Flat Cable Wiring Board