





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	0	D		REVISED PER ECO-08-008919	16APR08	HMR DB

- 1 MATERIAL: CONNECTOR- NYLON UL94V-2 (BLUE).
CONTACTS- 0.30 [.012] THK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203 [.000080] MIN THK).
(MATTE TIN 0.00203 [.000080] MIN THK).
- 2 CONTACTS ACCEPT #26 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX INSULATION DIA.
- 3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.
- 4 HOUSING FEATURES: FEED-THRU.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.



SECTION A-A

TIN	91.14	[3.588]	95.20	[3.748]	99.06	[3.900]	24	5-641526-4
	55.47	[2.184]	59.54	[2.344]	63.40	[2.496]	15	4-641526-5
	43.59	[1.716]	47.65	[1.876]	51.51	[2.028]	12	4-641526-2
	31.70	[1.248]	35.76	[1.408]	39.62	[1.560]	9	3-641526-9
	19.81	[.780]	23.88	[.940]	27.74	[1.092]	6	3-641526-6
	11.89	[.468]	15.95	[.628]	19.81	[.780]	4	3-641526-4
	7.92	[.312]	11.99	[.472]	15.85	[.624]	3	3-641526-3
	3.96	[.156]	8.03	[.316]	11.89	[.468]	2	3-641526-2
	91.14	[3.588]	95.20	[3.748]	99.06	[3.900]	24	2-641526-4
TIN-LEAD	55.47	[2.184]	59.54	[2.344]	63.40	[2.496]	15	1-641526-5
	43.59	[1.716]	47.65	[1.876]	51.51	[2.028]	12	1-641526-2
	31.70	[1.248]	35.76	[1.408]	39.62	[1.560]	9	641526-9
	19.81	[.780]	23.88	[.940]	27.74	[1.092]	6	641526-6
	11.89	[.468]	15.95	[.628]	19.81	[.780]	4	641526-4
	7.92	[.312]	11.99	[.472]	15.85	[.624]	3	641526-3
	3.96	[.156]	8.03	[.316]	11.89	[.468]	2	641526-2
	91.14	[3.588]	95.20	[3.748]	99.06	[3.900]	24	2-641526-4
	55.47	[2.184]	59.54	[2.344]	63.40	[2.496]	15	1-641526-5
FINISH	C		B		A		NO. OF CIRCUITS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B. LEWIS
CHK
R. SWING
APVD
-

5-31-96
5-31-96

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -

SEE NOTE 1

PRODUCT SPEC
APPLICATION SPEC
-

SIZE
A1

WEIGHT
-

CAGE CODE
00779

DRAWING NO
641526

RESTRICTED TO
-

NAME
MTA-156
POSTED CONNECTOR ASSEMBLY,
26 AWG

SCALE
5:1

SHEET
1 OF 1

REV
D

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

CUSTOMER DRAWING