





$\phi 6 \pm .20$
($\phi .236 \pm .008$)

MAXI Fuse Rating

Fuse Rating (Colors)	Wire (AWG)
20A (Yellow)	12AWG
30A (Green)	10AWG
40A (Orange)	8AWG
50A (Red)	8AWG
60A (Blue)	6AWG



Dimensions: mm (in.)

SPECIFICATIONS

- Rating: 60A max 12/24/32 VDC
- Insulation Resistance: 500VDC 100M Ω Min.
- Dielectric Strength: 1000VAC 1 min.
- Operating Temperature: -25°~85°C
- Fuse Type: Maxi Fuse
- RoHS Compliant

MATERIALS

- Frame: Nylon 66 FR7025, Black
- Terminal: Copper
- Nut: Nickel Plated Metal
- Screw: M5x0.8 L=5.8mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-R372-GR](#)