


DUAL FULL-BRIDGE PWM MOTOR DRIVERS

UDN2916B/EB AND UDN2917EB

FEATURES


- 750 mA (UDN2916B/EB) or 1.5 A (UDN2917EB) Continuous Output Current
- 45 V Output Sustaining Voltage
- Internal Clamp Diodes
- Internal PWM Current Control
Linear Input for Micro-Stepping, or External μ P Selection at 0, 33, 67, or 100%
- Low Output Saturation Voltage
- Internal Thermal Shutdown

UDN2916B




Dwg. PP-005

UDN2916EB



Dwg. PP-006

UDN2917EB



Dwg. PP-021