










IDC Cap

NKJ-6501	Black
NKJ-6502	Blue
NKJ-6503	Red
NKJ-6504	Orange
NKJ-6505	Yellow
NKJ-6506	Green
NKJ-6507	Ivory
NKJ-6508	White



Physical Specification

Jack housing:ABS high-impact UL94V-0 thermoplastic

Spring wire:Phosphor Bronze C5210 temper wire 50u" Gold over 100u" Nickel undercoat

IDC housing:Polycarbonate resin high-impact UL94V-0 thermoplastic

IDC contact:Phosphor Bronze C5191R-H, t=0.4mm,200u" Tin over 50u"Nickel undercoat

Insertion Life:750 mating cycles with FCC compliant RJ-45 plug

Contact force:100 grams with FCC compliant RJ-45 plug

Plug retention force:11 lbf min

Durability:200 termination cycles


Contact compatibility:Accommodates 22 to 26 AWG solid/24 AWG stranded

Operating Temperature Range:-10℃ to 60℃

Storage Temperature Range:-40℃ to 68℃

Humidity:10%~90%RH



Scale	1:1		 Quest Technology Int'l, Inc 11200NW 138th st, Medley, FL33178		
3rd Angle Projection					
Unit	mm				
Date	2011.12.14				
Tolerance					
-20 ±0.2	-50 ±0.4	-150 ±0.5	150~ ±1.5	ALGLE 2°	