





PART NUMBER	ITEM ①	ITEM ②
142-0003-201	BODY BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	CRIMP SLEEVE COPPER GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN
142-0003-206	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	COPPER NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN



DRAWING NO.									
C - 142-0003-201/210									
0	REVISIONS								
CHANGED: REVISED AND REDRAWN. WAS "C" SIZE, DATED 11-26-86.									
02	05-16-88	EJ	RRFRJB	05-19-88	ECO 23380				
VAX VERSION UPDATE.									
03	08-04-88	EJ	RRFRJB	8-10-88	ECO 23513				
VERSION UPDATE									
4	5-10-93	RH	888888	888888	ECO 41659				

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED PER ANSI Y 14.5M - 1982

"μSTATION"

COMPANY CONFIDENTIAL

NOTES:

1. SPECIFICATIONS:

CABLE ACCEPTABILITY: RG 188/U, RG 316/U, RG 161/U

RG 174/U, RG 179/U, RG 187/U

CABLE HEX CRIMP SIZE: .128

CABLE RETENTION: 20 LBS

IMPEDANCE: 50 OHMS

TOLERANCE UNLESS OTHERWISE SPECIFIED	DRAWN BY EJ	DATE 7-31-87	JOHNSON[®] Cinch Connectivity Solutions 299 Johnson Ave. Ste. 100 Waseca, MN 56093 1-800-247-8256	
DECIMALS .XX	CHECKED BY	DATE		
.XXX	APPROVED BY RRF	DATE 5-16-88	TITLE CABLE TERMINATION STRAIGHT PC MOUNT RG 316	
MATL	APPROVED BY RJB	DATE 5-16-88		
FINISH	RELEASE DATE	DATE 5-19-88	CODE NO.	DRAWING NO. C - 142-0003-201/210
			SCALE 10:1	U/M INCH SHEET 2 OF 2