



FEATURES:

- Ideal for use as a temporary jumper wire.

MATERIALS:

Conn: Insulated Microgator Clip

Material: Solid copper.

Insulation: Vinyl.

Color: Matches color of wire.

Wire: 20 AWG stranding 41 x 36 t.c., PVC insulated, 2.21 (.087) O.D.

Marking: "POMONA 1613-XX"

RATINGS:

Operating Temperature: +50°C. (+122° F.) Max.

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 1613-XX-*

XX = Cable Lengths, Standard Lengths: 4" (102), 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths and colors can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 1613-60-2 Indicates 60" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA