

CATALOG LISTING
1TP67-L4 SERIES CHART 1
PAGE 1 OF 1

ISSUE
3

REVISIONS
A C092162
JAK
5 MAR 98
B C094412
DLM
13 OCT 99


FORMTEK
DRAWN
KDR 10 JUN 94
CHECK KAG 23 JUN 94
CHECK

MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH-ROCKER FLUSH KEY

CATALOG LISTING
1TP67-L4 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL DATA
	LUG SIDE (1-2)	CENTER (1-2)	OPPOSITE LUG (2-3)	
ITP67-1-L4	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC 1HP 250, 277 VAC 5A 125 VAC "L"
ITP67-2-L4	OFF	NONE	ON	
ITP67-3-L4	ON	NONE	ON	
ITP67-21-L4	NONE	OFF	ON	
ITP67-31-L4	NONE	ON	ON	
ITP67-4-L4	MOM OFF	NONE	ON	L192 10A 125, 250, 277 VAC 1/4HP 125 VAC, 1/2HP 250, 277 VAC 3A 125 VAC "L"
ITP67-5-L4	MOM ON	OFF	ON	
ITP67-6-L4	MOM ON	NONE	OFF	
ITP67-7-L4	MOM ON	OFF	MOM ON	
ITP67-8-L4	MOM ON	NONE	ON	
ITP67-51-L4	NONE	ON	MOM ON	
ITP67-61-L4	MOM ON	OFF	NONE	

UL ® CE

UL ® CE

NOTES
1 - MICRO SWITCH CAT LISTING MARKED ON SIDE OF SWITCH
2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
3 - SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE UNLESS NOTED. TOLERANCES ARE:

	DIM	TOL	DIM	TOL
	mm	mm/in	in	mm/in
NO PLACES	X	1/32	X	0.003
ONE PLACE	X X	0.001	X X	0.001
TWO PLACES	X X X	0.0005	X X X	0.0005
THREE PLACES	X X X X	0.0001	X X X X	0.0001

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT