

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [85071-0100](#)
Status: **Active**
Description: 4.00mm SRC Heavy Duty Receptacle Housing, 84 Way, Black

Documents:

- | | |
|--|--|
| Drawing (PDF) | Packaging Specification PK-85071-001 (PDF) |
| Product Specification PS-85070-001 (PDF) | Test Summary STR-1193 (PDF) |
| Application Specification AS-85070-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

Product Family	Crimp Housings
Series	85071
Application	Power, Wire-to-Wire
Comments	Polarized to mating part
Product Name	SRC

Physical

Circuits (maximum)	84
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	14
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	40A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-85070-001
Packaging Specification	PK-85071-001
Product Specification	PS-85070-001
Sales Drawing	SD-85071-100
Test Summary	STR-1193



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[85071Series](#)

Mates With

[85070](#) SRC Heavy Duty Connector

Use With

[33000](#) Male Terminals, Tin, AWG 1422.
[33011](#) Male Terminal, Gold, AWG 1422.
[19431](#) Male Terminal, Tin, AWG 812

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

85071-0100