

Twist-Lock® Devices

20 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

Insulgrip® Connector Bodies and Receptacles

**20A 3ØY
120/208V AC**
NEMA L21-20R
UL/CSA
2 HP



**20A 3ØY
277/480V AC**
NEMA L22-20R
UL/CSA
5 HP



**20A 3ØY
347/600V AC**
NEMA L23-20R
UL/CSA

Connector Bodies**Watertight Safety-Shroud®****IP66** SUITABILITY

Description	Cord Dia.	Catalog Numbers
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2513SW - -

**HBL2513SW****Insulgrip****IP20** SUITABILITY

Description	Cord Dia.	Catalog Numbers
Black and white nylon.	.35"-1.15" (9-29)	HBL2513 HBL2523 HBL2533
All black nylon.	.35"-1.15" (9-29)	HBL2513BK - -
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL25CM13 - -
Black and white for flat cable.	.35"-1.15" (9-29)	HBL2513FC - -

**HBL2513**

Accessories on page B-53.

Receptacles**Watertight Safety-Shroud, Back Wired****IP66** SUITABILITY

Description	Catalog Numbers
Gray Valox® housing and flange.	HBL2510SW - -

Accessories on page B-54.

Safety-Shroud Twist-Lock, Back Wired**IP20** SUITABILITY

Description	Catalog Numbers
Gray Valox® angle housing, one gang.	HBL2510AR - -
Gray Valox® surface mounting, one gang.	HBL2510SR - -
Gray Valox® semi-flush, two gang.	HBL2510SR2 - -

Accessories on page B-54.

Single Flush, Back and Side Wired**IP20** SUITABILITY

Description	Catalog Numbers
Black nylon face.	HBL2510 HBL2520* HBL2530*
Isolated ground, orange nylon face.	IG2510 - -





Accessories on page B-52.

Insulgrip Flanged Receptacles

Description	Catalog Numbers
Nylon casing, back wired.	HBL2516 HBL2526 HBL2536

Accessories on page B-52.

Note: * Not Fed Spec.

**HBL2510SW****HBL2510AR****HBL2516****HBL2510****HBL2510SR2****HBL2510SR**

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.