

PANEL MOUNT INDICATOR, NON-RELAMPABLE

LED TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
LED 12V SERIES				
WL-1091QM1-12V	RED	12V-14V	20mA	100,000
WL-1091QM5-12V	GREEN	12V-14V	20mA	100,000
WL-1091QM7-12V	YELLOW	12V-14V	20mA	100,000
LED 24V SERIES				
WL-1091QM1-24V	RED	24V-28V	20mA	100,000
WL-1091QM5-24V	GREEN	24V-28V	20mA	100,000
WL-1091QM7-24V	YELLOW	24V-28V	20mA	100,000

NOTES

1. Recommended panel thickness
0.030" to 0.090"
2. .187" terminals are standard
3. Storage temperature
 T_{STG} : -25°C - +80°C
4. Ambient temperature
 T_A : -20°C - +60°C
5. DC operation only
6. Voltage tolerance
 V_{OP} : $\pm 10\%$
7. Body material
Nylon, white
8. Lens material
Polycarbonate
9. Bezel material
Stainless steel
10. Anode (+)
Marked above terminal
11. .250 quick connects
available upon request


CERTIFICATIONS

UL (E340667), RoHS



RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

