

19" chassis - *multipacPRO* ServicePLUS

Individual components 19" chassis for non-standardised assemblies

- Please select:
 - Height and depth of basic kit (1 ... 5 U, it102
 - ems 1+2+5)
 - Mounting plate
 - Top cover/base plate (item 3+4)
 - Front handles
 - EMC gasketing kit
 - Telescopic slides
- In accordance with IEC 60297-3-105

Order Information

				Basic kit	Mounting plate	Top cover/base plate	
						plain	perforated
h = clear height (overall) (H - 8.1 mm) b = clear installation width = 403 mm 06008052				06002004 1 x Al front panel, 3 mm; 2 x extruded Al side panels; 1 x Al rear panel, 2 mm, incl. fixing material kit	06002058 Al plate, 2 mm, depth = D - 70 mm; threaded insert, St, 2 mm, zinc-plated, height 7 mm, length 431.3 mm, M3 hole clearance 1 HP = 5.08 mm; for heavy equipment	06002053 is inserted into the basic kit, Al, 1 mm, passivated; please order EMC gasketing kit separately	06007050 is inserted into the basic kit, Al, 1 mm, passivated; hole diameter 4 mm, perforation ratio 58 %
Height U	Height mm	Width HP	Depth D mm	PU 1 kit	1 piece	1 piece	1 piece
1	43.7	84	220	20860-201	20860-107	30860-501	30860-510
1	43.7	84	280	20860-202	20860-108	30860-502	30860-511
1	43.7	84	340	20860-203	20860-109	30860-503	30860-512
2	88.1	84	220	20860-210	20860-107	30860-501	30860-510
2	88.1	84	280	20860-211	20860-108	30860-502	30860-511
2	88.1	84	340	20860-212	20860-109	30860-503	30860-512
3	132.6	84	280	20860-219	20860-108	30860-502	30860-511
3	132.6	84	340	20860-220	20860-109	30860-503	30860-512
3	132.6	84	400	20860-221	20860-110	30860-504	30860-513
3	132.6	84	460	20860-222	20860-111	30860-505	30860-514
4	177.0	84	280	20860-228	20860-108	30860-502	30860-511
4	177.0	84	340	20860-229	20860-109	30860-503	30860-512
4	177.0	84	400	20860-230	20860-110	30860-504	30860-513
4	177.0	84	460	20860-231	20860-111	30860-505	30860-514
5	221.5	84	460	20860-240	20860-111	30860-505	30860-514