


Item # C15A1P-80VDC, 15 Amp 1 Pole UL 489A Rated DIN Rail Mounted Circuit Breaker

UL 489A
DIN Rail mounted
Compact 13 mm width
One Pole only
Current rating up to 50 A
100% Rating capability
Hydraulic-Magnetic technology
Trip curve U2 standard



· [SPECIFICATIONS](#) · [CERTIFICATIONS](#)

SPECIFICATIONS

Current	15 A
Width	13 mm
Numbers of Poles	1
Maximum Voltage	80 VDC
Minimum Amp Rating	1 A
Maximum Amp Rating	50 A
Interrupting Cap.	10,000 A
Dielectric Strength	1500 V, 50/60 Hz
Insulation Resistance	100 MΩ

Operating Temp. Range	-40 to +60 °C
Units Per Package	1

CERTIFICATIONS

Certifications	 CE  CSA  RoHS (EU directive 2002/95/EC)  UL Recognized  VDE
---------------------------	---