




















FEMALE MALE	VERTICAL PC TAIL		VERTICAL SMT	CRIMP	
	SIL	DIL	DIL	SIL	DIL
VERTICAL PC TAIL	M80-840 M80-897  7.23	M80-850 M80-887  7.23	M80-681  7.85	M80-898 M80-899  10.2 max.	M80-888 M80-889  10.2 max.
	M80-805 M80-852 M80-877 M80-879 M80-881 M80-882	M80-815 M80-853 M80-854 M80-863 M80-867 M80-869	M80-815 M80-853 M80-854 M80-863 M80-867 M80-869	M80-805 M80-852 M80-877 M80-879 M80-881 M80-882	M80-815 M80-853 M80-854 M80-863 M80-867 M80-869
HORIZONTAL PC TAIL	M80-840 M80-897  7.98	M80-850 M80-887  9.98	M80-681  10.60	M80-898 M80-899  11.1 max.	M80-888 M80-889  13.1 max.
	M80-804 M80-842 M80-843 M80-846 M80-879 M80-878	M80-814 M80-839 M80-841 M80-851 M80-866 M80-868	M80-814 M80-839 M80-841 M80-851 M80-866 M80-868	M80-804 M80-842 M80-843 M80-846 M80-879 M80-878	M80-814 M80-839 M80-841 M80-851 M80-866 M80-868
VERTICAL SMT		M80-850 M80-887  7.85	M80-681  8.45		M80-888 M80-889  10.50
		M80-826 M80-827 M80-828	M80-826 M80-827 M80-828		M80-826 M80-827 M80-828
HORIZONTAL SMT		M80-850 M80-887  11.85	M80-681  12.45		M80-888 M80-889  14.50
		M80-665 M80-666 M80-667	M80-665 M80-666 M80-667		M80-665 M80-666 M80-667
CRIMP		M80-850 M80-887  10.94 max.	M80-681  11.28		M80-888 M80-889  13.60 max.
		M80-812 M80-813 M80-816 M80-817	M80-812 M80-813 M80-816 M80-817		M80-812 M80-813 M80-816 M80-817

