



Commercial Spec Grade Duplex Receptacle, Side Wire 20amp
125volt, Gray

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Ivory	UPC Number	785007119169
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus Listing Number	140596
--------------	-----	----------------------	--------

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Wire Ground	Wire Size	4 AWG
Number of Wires	3		
