



Metal Working Tools - Chop Saws

D28700



D28700 Features

- Horizontal handle for superior ergonomics and less user fatigue
- Spindle lock for quick and easy wheel change
- Quick release clamp results in less time in changing the work piece

D28700 Specifications

Power Input	2200 Watts
Power Output	1350 Watts
No Load Speed	3800 rpm
Wheel Diameter	355 mm
Max. Cutting Capacity at 90° [Square Profile]	119 x 119 mm
Max. Cutting Capacity at 90° [Rectangular Profile]	115 x 130 mm
Max. Cutting Capacity at 90° [L-Shape Profile]	137 x 137 mm
Max. Cutting Capacity at 90° [Rounded Profile]	115 mm
Max. Cutting Capacity at 45° [Square Profile]	98 x 98 mm
Max. Cutting Capacity at 45° [Rectangular Profile]	115 x 98 mm
Max. Cutting Capacity at 45° [L-Shape Profile]	98 x 98 mm
Max. Cutting Capacity at 45° [Rounded Profile]	98 mm
Weight	16 kg
Length	486 mm
Height	378 mm

D28700 Standard

- Metal cutting disc
- Hex key