







MATERIAL NUMBER	OLD PART NUMBER
1201140087	BTY8030-FBB

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-25°C TO +90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR

DESCRIPTION EC NO: WEU2010-0452 DRWN: BBRAUCH 2010/03/23 CHK'D: FP APPR: FPACHER 2010/03/24	QUALITY SYMBOLS ▽ = 0 ⌒ C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
					MM ONLY		2:1	METRIC		
					DRAWN BY DATE		MICRO-CHANGE MPIS TOP MOUNT 8PORT NO LED ----			
					BBRAUCH 2010/03/23					
					CHECKED BY DATE					
					FP 2010/03/23					
					APPROVED BY DATE					
1	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			FPACHER 2010/03/23		 MOLEX INCORPORATED			
					MATERIAL NO.			DOCUMENT NO.	SHEET NO.	
					see table			SD-120114-090		1 OF 1
			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			A2							