




STYLE B
INSULATION RESTRICTING

100	LOOSE PIECE, BOX	16-14	.105-.150	16-14	--	A	4 5	8-320564-1	
500	320564 ON TAPE	16-14	.105-.150	16-14	--	A		2-320564-3	
500	LOOSE PIECE	14	.078-.130	14	GREEN	B		10 2-320564-2	
500	LOOSE PIECE	16	.063-.130	16	BLUE	B		9 2-320564-1	
500	LOOSE PIECE	16-14	.105-.150	16-14	--	A		8 320564	
QTY	PACKAGE TYPE	STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY	SLEEVE	PART NO
							FINISH		

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	13JAN10	TE TE Connectivity			
	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES FINISH	CHK T MICHELUTTI	13JAN10				
			APVD T MICHELUTTI	13JAN10	SIZE CAGE CODE DRAWING NO RESTRICTED TO	A2 00779 C-320564 -		
VOLTAGE RATING: 300 VOLT MAX			PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -			
CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED OR SOLID		MATERIAL	6					

IS A CONTROLLED DOCUMENT FOR
ATED, IT IS SUBJECT TO CHANGE
ROLLING MANUFACTURING ORGANIZATION
NACTED FOR THE LATEST REVISION.

CUSTOMER DRAWING

SCALE 5:1 SHEET 1 OF 1 REV N