








- 1 MATERIAL: ITEM NO. 1: HOUSING - ZINC DIECASTING, NICKEL PLATED
ITEM NO. 2: CONTACT BODY - PUR, PA
ITEM NO. 3: CONTACT - CuSn (bronze)
CONTACT FINISH - Au (gold)
- 2 ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED
- 3 MEASUREMENT REFERENCE ONLY
- 4 PACKAGING: 1 PIECE IN A BAG

TECHNICAL DATA	3-2271138-2	4-2271138-2
RATED VOLTAGE	250V	125V
RATED IMPULSE VOLTAGE	2500V	1500V
POLLUTION DEGREE	3	3
OVERVOLTAGE CATEGORY	II	II
MATERIAL GROUP	II	II
RATED CURRENT	4A	4A
VOLUME RESISTIVITY	≤ 3mΩ	≤ 3mΩ
DEGREE OF PROTECTION	IP68	IP68
UPPER TEMPERATURE	+85 °C	+85 °C
LOWER TEMPERATURE	-40 °C	-40 °C



3-2 AS SHOWN
WIE GEZEICHNET

24 / 0.25mm ²	⚠	5	4-2271138-2
24 / 0.25mm ²	⚠	4	3-2271138-2
WIRES AWG / mm ²	MATERIAL	NUMBER OF POLES	TE-PART-NO.

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:
MASSE/MASSSTAB:
1:1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES/WINKEL ±
FINISH/OBERFLÄCHE/FARB

DWN YASHKUMAR 29APR2014
CHK M.STRELOW 29APR2014
APVD C.SCHREITLINGER 29APR2014

PRODUCT SPEC
PRODUKTSPEZ.
-
APPLICATION SPEC
VERARBEITUNGSSPEZ.
-
WEIGHT
GEWICHT
-
Customer Drawing

NAME
M12 PANEL MOUNT RECEPTACLE CONNECTOR
B-CODING

SIZE
A2

CAGE CODE
00779

DRAWING NO.
ZEICHNUNGS-NR.
C-2271138

RESTRICTED TO
NUR FÜR
-
REV
A1

TE Connectivity

SCALE
MASSSTAB
2:1

SHEET
BLATT
1 OF 1

REV
A1