

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

AMP PART NO	MATERIAL	PKG TYPE	QTY
8-36959-3	M/F 8-36959-0	BOX	25

LOC	DIST
G	14

F	ZONE	LTR

REVISIONS			DATE	APPD
REVISED & REDRAWN PER	0720-0037-93	5/24/93	OF 5	PER


METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	E13288 Listed
3/0 AWG SOLID OR STRANDED	3/0 AWG SOLID OR STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
3/0 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 3/0W* APPROX AS SHOWN
2 MATERIAL THK: 2.31±0.08 [.091±.003]



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

CIRCULAR MIL AREA:
76.3-96.3mm² [150,500-190,000] CIR MILS
SOLID OR STRANDED

FINISH: T1N PLATE
0.00254 [.000100] MIN THK PER MIL-T-10727

DO NOT SCALE PRINT. UNLESS SPECIFIED
TOLERANCES ON:
2 PLG DEC ± 0.201.0003
3 PLG DEC ± -
ANGLES ± -

DR S/24/93	DK SCHW
CHK 1/27/94	RD WEIN
APPD 1/27/94	RE ROGER
APPD 1/27/94	J. MCKLEY

AMP Incorporated	AMP Incorporated
Harrisburg, PA 17105-3608	Harrisburg, PA 17105-3608
SPLICE, BUTT, SOLISTRAND™	SPLICE, BUTT, SOLISTRAND™

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS
1-800-522-6752

FOR APPLICATION TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

AMP 1470-15 REV 3-92

04-FEB-94 07:46:10 00026463 /files/dept1123/dwg1123/u.solistrand/u.butt-splice

CUSTOMER DRAWING