


Tab Contacts

**Tabs 1.6 x 0.6 mm
with Steel Top Spring,
Mates with
Micro Timer II and
Micro Timer III**

Product Specification:
108-18331

Application Specification:
114-18082



Standard Tab Contacts

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.2-0.5	-	1.15-1.60	-1 / -2 / -3	963898 "	7,000	963899 "	500	x-878607-x	539651-2
0.5-1.0	-	1.4-2.1	-1 / -2 / -3	963900 "	6,000	963901 "	500	x-878608-x	

Tab Contacts with Single Wire Sealing System

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish *	Part Numbers					Hand Tool 539635-1 with Die Set
	FLK (mm)	FLR (mm)		Strip Form	Packaging Unit	Loose- Piece	Packaging Unit	Applicator *	
0.2-0.5	-	1.15-1.60	-1 / -2 / -3	963902 "	4,000	963903 "	500	x-878615-x	539651-2
0.5-1.0	-	1.4-2.1	-1 / -2 / -3	963904 "	4,000	963905 "	500	x-878616-x	

***) Material and Finish:**
xxx-1 = CuSn4, pre-tin plated
xxx-2 = CuFe2, pre-tin plated
xxx-3 = CuSn4, gold plated

Remarks:
1) = With Spring 1

♦) The pre- and suffix for the applicators depends on the applied termination equipment.