

3-Wire Cordsets, Standard Plug Body

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout	
	RK 4T-*	RS 4T-*	AWM PVC Grey, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50528-*M [†] , flexlife*		
	WK 4T-*	WS 4T-*			
	RK 4T-*/S90	RS 4T-*/S90	AWM TPU Grey, 3x20 AWG, 90°C, 5.1 mm OD, Cable #RF50518-*M [†] , Cut/Abrasion Immune		
	WK 4T-*/S90	WS 4T-*/S90			
	RK 4T-*/S101	RS 4T-*/S101	AWM TPE Grey, 3x20 AWG, 105°C, 5.7 mm OD, Cable #RF50940-*M [†] , flexLife-20, High Flex Over 20 Million Cycles		
	WK 4T-*/S101	WS 4T-*/S101			
	RK 4T-*/S529	RS 4T-*/S529	TPU/Heavy Braid Double Jacket Yellow, 3x20 AWG, 90°C, 5.1 mm OD, Cable #RF50832-*M [†] , Cut/Abrasion Immune Braided Mechanical Shield		
	WK 4T-*/S529	WS 4T-*/S529			
	RK 4T-*/S824	RS 4T-*/S824	PLTC AWM PVC Grey, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50829-*M [†] , Tray Rated		
	WK 4T-*/S824	WS 4T-*/S824			
	RK 4T-*/S715	RS 4T-*/S715	AWM PVC Yellow, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50674-*M [†] , flexlife		
	WK 4T-*/S715	WS 4T-*/S715			
	RK 4T-*/S760	RS 4T-*/S760	AWM PVC Black, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50795-*M [†] , flexlife		
	WK 4T-*/S760	WS 4T-*/S760			
	RK 4T-*/S618	RS 4T-*/S618	ITC/PLTC PVC Grey, 3x20 AWG, Foil/Drain, 105°C 5.7 mm OD, Cable #RF50611-*M [†] , RFI/EMI Shielding, tray rated		
	WK 4T-*/S618	WS 4T-*/S618			

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKV .." indicates stainless steel.

† See Section N for **reelfast**® cable information.