



THIS DOCUMENT CONTAINS DATA PROPRIETARY
TO PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.
IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.5	W
MAX INPUT POWER	0.8	W
IMPEDANCE	45±15%	OHM
OUTPUT SPL @ 1W/0.5M (AT 0.8, 1.0, 1.2, 1.5 kHz)	90±3	dBA
DISTORTION	5%	—
RESONANT FREQUENCY	350±20%	Hz
FREQUENCY RANGE	350 ~ 8,000	Hz
HOUSING MATERIAL	METAL	—
CONE MATERIAL	PAPER	—
MAGNET MATERIAL	FERRITE	—
OPERATING TEMPERATURE	-20 ~ +60	°C
WEIGHT	48	grams



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE
OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AS7045.DWG

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	4/15/03	
A	REVISED TO NEW TEMPLATE	4/15/04	R. W.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
TOLERANCES ARE ±0.5 AND ANGLES ARE
±3°.

APPROVALS	DATE
DRAWN T. P. I.	4/03
APPROVED S. J.	4/03

DO NOT SCALE DRAWING

projects®
unlimited

Dayton, Ohio

DYNAMIC SPEAKER
AS7045

SIZE A DRAWING NO.
AS7045

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS7045](#)