


SOLISTRAND Ring Tongue Terminals



Terminal Body: Copper per ASTM B-152, tin plated per MIL-T-10727.


Stock No.	Mfr.'s Type	Style	AWG	Stud Size	Width (In.)	PER PK./1000		
						1-4	5-9	10-24
512-8580	34104	A	22-16	4	0.218	69.18	57.65	49.41
512-4182	34105	A	22-16	6	0.218	45.00	41.54	39.00
512-4184	34108	A	22-16	8	0.281	55.88	47.90	44.70
512-4186	34109	A	22-16	10	0.281	67.05	55.88	47.90
512-4284	34113	A	22-16	1/4	0.469	78.38	65.31	55.98
512-1569	34115	A	22-16	3/8	0.531	83.31	69.43	59.51
512-4286	34120	A	16-14	6	0.250	67.05	55.88	47.90
512-4289	34122	A	16-14	8	0.343	67.05	55.88	47.90
512-4290	34123	A	16-14	10	0.343	67.05	55.88	47.90
512-4292	34124	A	16-14	1/4	0.469	78.38	65.31	55.98
512-1571	34125	A	16-14	5/16	0.469	80.89	67.41	57.78
512-1572	34126	A	16-14	3/8	0.531	99.33	82.77	70.95

Stock No.	Mir.'s Type	Style	AWG	Stud Size	Width (In.)	PER PK./500		
						1-4	5-9	10-24
512-1573	35476	A	12-10	6	0.281	49.57	41.31	35.41
512-4294	32994	A	12-10	8	0.375	48.06	40.05	34.33
512-4296	33457	A	12-10	10	0.375	39.98	33.32	30.76
512-4298	33458	A	12-10	1/4	0.531	55.18	45.99	39.42
512-1574	33459	A	12-10	5/16	0.531	57.02	47.52	40.73
512-1575	33220	A	12-10	3/8	0.593	57.02	47.52	40.73

Stock No.	Mfr.'s Type	Style	AWG	Stud Size	Width (In.)	PER PK./100		
						1-4	5-9	10-24
512-1576	35247	A	8	1/4	0.594	36.79	33.11	27.59
512-1578	33462	A	8	5/16	0.594	36.79	33.11	27.59
512-1579	33463	A	8	3/8	0.594	37.97	34.17	28.48
512-1581	33465	C	6	1/4	0.625	24.80	22.32	18.60
512-1583	33466	C	6	5/16	0.625	33.95	30.56	25.47
512-1584	33467	C	6	3/8	0.625	33.95	30.56	25.47
512-1585	33468	A	4	10	0.656	51.49	46.61	42.91
512-1587	33469	A	4	1/4	0.656	47.01	42.31	35.26
512-8579	33470	A	4	5/16	0.656	47.01	42.31	35.26
512-1588	33471	A	4	3/8	0.656	57.21	51.49	42.91


Stock No.	Mfr.'s Type	Style	AWG	Stud Size	Width (In.)	PER PK./50		
						1-4	5-9	10-24
512-1589	330301	B	2	10	0.625	52.24	47.01	39.18
512-1591	320383	B	2	1/4	0.625	38.67	34.80	29.00
512-1592	322870	B	2	5/16	0.625	34.95	31.46	26.21
512-1593	321600	B	2	3/8	0.625	35.26	29.38	25.19
512-1595	320741	D	2	7/16	0.890	39.28	32.73	28.06
512-1598	36915	C	1/0	1/4	0.875	59.59	49.66	42.56
512-1601	36917	C	1/0	3/8	0.875	52.79	43.99	37.70
512-1602	36919	C	1/0	1/2	0.875	61.49	51.24	43.92
512-1607	36923	C	2/0	3/8	0.946	75.28	62.73	53.77
512-1608	36925	C	2/0	1/2	0.946	75.28	62.73	53.77
512-1610	322224	C	2/0	5/8	1.270	172.16	143.46	122.97

SOLISTRAND Flanged Spade Tongue Terminal



Stock No.	Mfr.'s Type	AWG	Stud Size	Width (In.)	PER PK./1000		
					1-4	5-9	10-24
512-1615	323136	22-16	6	0.250	263.51	219.59	188.22

SOLISTRAND Butt Splices



Stock No.	Mfr.'s Type	Style	AWG	O.D. Max. (In.)	Length (In.)	I.D. Min. (In.)	PER PK./1000		
							1-4	5-9	10-24
512-1617	321198	Strap	26-22	0.082	0.385	0.031	107.73	96.96	80.80
512-1619	324001	Strap	24-20	0.105	0.490	0.043	112.22	101.00	84.17
512-4337	31818	Standard	22-16	0.141	0.578	0.061	86.70	78.03	65.03
512-1620	330367	Sight Hole	22-16	0.165	0.578	0.085	153.68	138.31	115.26
512-1621	327025*	Strap	16-14	0.165	0.591	0.085	176.94	159.24	132.70
512-1623	330368	Sight Hole	16-14	0.165	0.567	0.085	169.71	152.73	127.28

*No wire stop.

Stock No.	Mfr.'s Type	Style	AWG	O.D. Max. (In.)	Length (In.)	I.D. Min. (In.)	PER PK./500		
							1-4	5-9	10-24
512-4339	31819	Standard	16-14	0.165	0.567	0.085	48.48	40.40	34.63
512-4341	32151	Standard	12-10	0.226	0.565	0.129	56.45	51.32	47.04

Stock No.	Mfr.'s Type	Style	AWG	O.D. Max. (In.)	Length (In.)	I.D. Min. (In.)	PER PK./100		
							1-4	5-9	10-24
512-1625	34322	Standard	6	0.369	1.015	0.232	46.35	42.14	35.65

PLASTI-GRIP Ring Tongue Terminal



Insulation: Vinyl. Terminal Body: Copper per ASTM B-152, tin plated per MIL-T-10727.

22-16 AWG — Red

Stock No.	Mfr.'s Type	Stud Size	Insulation Dia. Max. (In.)	PER PK./1000		
				1-4	5-9	10-24
512-1559	34140	2	0.140	117.20	97.67	83.71
512-4008	34141	4	0.140	117.20	97.67	83.71
512-4010	34142	6	0.140	117.20	97.67	83.71
512-4015	34144	6	0.140	117.20	97.67	83.71
512-4020	34145	8	0.140	63.57	52.97	45.40
512-4025	34146	10	0.140	117.20	97.67	83.71
512-1561	32952	10	0.140	117.20	97.67	83.71
512-4028	34149	10	0.140	112.69	93.91	80.49
512-4030	34150	1/4	0.140	137.01	114.17	97.86
512-4034	34152	3/8	0.140	141.17	117.64	100.83

16-14 AWG — Blue

512-4035	34158	6	0.170	117.20	97.67	83.71
512-4040	34160	8	0.170	63.57	52.97	45.40
512-4045	34161	10	0.170	112.69	93.91	80.49

PLASTI-GRIP Spade Tongue Terminals



Insulation: Vinyl. Terminal Body: Copper per ASTM B-152, tin plated per MIL-T-10727.

22-16 AWG — Red

Stock No.	Mfr.'s Type	Stud Size	Insulation Dia. Max. (In.)	PER PK./1000		
				1-4	5-9	10-24
512-4060	320665	6	0.140	97.67	83.71	78.13
512-4065	34155	8	0.140	117.20	97.67	83.71
512-4066	34156	10	0.140	117.20	97.67	83.71

16-14 AWG — Blue

512-4080	322994	6	0.145	97.67	83.71	78.13
512-4085	34167	10	0.170	117.20	97.67	83.71