

**Specifications:**

|                       |                                   |
|-----------------------|-----------------------------------|
| Sound level Category  | Medium Sound Level                |
| Mode of Operation     | Dual Tone                         |
| Mounting              | Panel (see note)                  |
| Voltage Rating        | 10 to 45 VDC                      |
| Frequency             | 1000 - 800 Hz                     |
| Loudness (Typical)    | 80 dB(A) @ 2 FT                   |
| Current Draw (max)    | 150 mA                            |
| Storage Temperature   | -40°C to +65°C                    |
| Operating Temperature | -30°C to +65°C                    |
| Weight (Typical)      | 78 g                              |
| Housing               | 6/6 Nylon, Color Black            |
| Options               | For other options contact factory |

**Dimensions: Inches (mm)**
