



Surface-Mount Analog Switches (Cont'd)

SO-8



Part Number	Analog Range (V)	$r_{DS(ON)}$ (Ω)	Switching Time t_{on} (ns)	ABS Max. Supply (V)	Configuration
DG417DY	± 15	35	175	44	SPST(1)
DG418DY	± 15	35	175	44	SPST(1)
DG419DY	± 15	35	175	44	SPDT(1)

SO-16



Part Number	Analog Range (V)	$r_{DS(ON)}$ (Ω)	Switching Time t_{on} (ns)	Max. ABS Supply (V)	Configuration
DG201ADY	± 15	175	600	44	SPST(4X)
DG211DY	± 15	175	1000	40	SPST(4X)
DG212DY	± 15	175	1000	40	SPST(4X)
DG221DY	± 15	90	550	44	SPST(4X)
DG271DY	± 15	50	60	44	SPST(4X)
DG308ADY	± 15	100	200	44	SPST(4)
DG309DY	± 15	100	200	44	SPST(4)
DG403DY	± 15	45	150	44	SPDT(4)
DG405DY	± 15	45	150	44	DPST(2)
DG411DY	± 15	35	175	44	SPST(4)
DG412DY	± 15	35	175	44	SPST(4)
DG413DY	± 15	35	175	44	SPST(4)
DG441DY	± 15	85	250	44	SPST(4X)
DG442DY	± 15	85	250	44	SPST(4X)
DG444DY	± 15	85	250	44	SPST(4X)
DG445DY	± 15	85	250	44	SPST(4X)
DG541DY	-5 to 8	60	70	19	SPST(4)
DG542DY	-5 to 8	60	100	19	SPDT(2)
DG601DY	0 to 12	35	45	22	SPST(4)