

"Stay Connected with Heyco" Strain Relief Bushings

HEYCO



Heyco® Original Strain Relief Bushings

Straight-Thru for Round Cables

.875" (22,2 mm) to 1.187" (30,1 mm) Mounting Holes


Fit 1/2" or 3/4" Electrical Knock-out Hole Sizes

- **Protects the lifeline of your electric/electronic products** by absorbing the forces of pull, push, and twist that may be exerted on the flexible power cord.
- Securely anchors, insulates, and protects cables at panel entry points.
- Sizes SR 7-Series to SR 9-Series for mounting hole diameters from .875" (22,2 mm) to 1.187" (28,6 mm).
- Sizes for thin .062" (1,6 mm) panel available:
SR 8N-2
See chart for details.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- Consult Heyco for other wire types and sizes.
- See pages 4-27 & 4-28 for SR assembly tools.


WILL FIT THESE CABLES				PANEL DIMENSIONS						PART NO.	DESCRIPTION	PART DIM.		Mounting Hole Plug
UL Type	AWG/ Conductors	Approximate Size		A Mounting Hole Dia.		B To Prevent Rotation		Finished Fit Panel Thickness*		Black		C BODY LENGTH		
		in.	mm.	in.	mm.	in.	mm.	in.	mm.			in.	mm.	PART NO.
SJ, SJT & SJO	16/2	.325	8,3											
	18/3	.330	8,4											
	14/2	.350	8,9	.875	22,2	.770	19,6	.125	3,2	1240	SR 7K-2	.750	19,1	2509
	16/3	.355	9,0											
	18/4	.360	9,1											
Same as SR 7K-2 above except				See Schematic				.125	3,2	1271	SR 7KR-2	.750	19,1	2509
SJT	14/3	.370	9,4											
	12/3	.425	10,8											
S, SO, & ST	18/2	.390	9,9	.875	22,2	.770	19,6	.125	3,2	1247	SR 7W-2	.750	19,1	2509
	18/3	.405	10,3											
	16/2	.405	10,3											
	16/3	.430	10,9											
Same as SR 7W-2 above except								.200	5,1	1250	SR 7L-2	.750	19,1	consult Heyco
SJT	12/3	.425-.475	10,8-12,1	.875	22,2	.840	21,3	.125	3,2	1497	SR 31-2	.812	20,6	2509
S & ST	14/2	.530	13,5											
	14/3	.560	14,2	.875	22,2	.840	21,3	.062	1,6	1254	SR 8N-2	.828	21,0	2509
	12/2	.600	15,3											
Same as SR 8N-2 above except								.125 .187	3,2 4,8	1260 1274	SR 8P-2 SR 8L-1	.812 .812	20,6 20,6	2509 consult Heyco
S	12/2	.600	15,2	1.093	27,7									
	12/3	.635	16,1	1.125	28,6									
	10/2	.640	16,3	1.093	27,7	1.000	25,4	.281	7,1	1287	SR 9P-2	1.000	25,4	2717
S, SO & ST	10/3	.690	17,5	1.187	30,2									
SRDT	12/4													

Standard color black. Consult Heyco for white and other colors.


*Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.




FOR SR-7KR-2 ONLY



STANDARD MOUNTING HOLES



ELONGATED MOUNTING HOLE



Quick
Specs

Material

Nylon 6/6

Certifications



Recognized under the Component Program of Underwriters' Laboratories File E15331



Certified by the Canadian Standards Association File 8919

Flammability Rating

94V-2

Temperature Range

-.04°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1274](#) [1271](#) [1254](#) [1250](#) [1287](#) [1240](#) [1247](#) [1260](#) [1497](#)