





LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	REDRAWN PER ECO-09-004892	06MAR09	HMR	JG
			H1	REVISED PER ECO-09-021826	07JAN10	KK	AEG

D

C

B

A



- 1

NO OF POSITIONS INDICATED PERTAINS TO THE HOUSING.
- 2

THIS COVER IS TO BE USED WITH 102536 .
- 3

MATERIAL: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK.
- 4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

D

C

B

A

OBSOLETE	91.44[3.600]	88.90[3.500]	35	72	3-102540-4
OBSOLETE	88.90[3.500]	86.36[3.400]	34	70	3-102540-3
OBSOLETE	86.36[3.400]	83.82[3.300]	33	68	3-102540-2
OBSOLETE	83.82[3.300]	81.28[3.200]	32	66	3-102540-1
OBSOLETE	81.28[3.200]	78.74[3.100]	31	64	3-102540-0
OBSOLETE	78.74[3.100]	76.20[3.000]	30	62	2-102540-9
OBSOLETE	76.20[3.000]	73.66[2.900]	29	60	2-102540-8
OBSOLETE	73.66[2.900]	71.12[2.800]	28	58	2-102540-7
OBSOLETE	71.12[2.800]	68.58[2.700]	27	56	2-102540-6
OBSOLETE	68.58[2.700]	66.04[2.600]	26	54	2-102540-5
OBSOLETE	66.04[2.600]	63.50[2.500]	25	52	2-102540-4
OBSOLETE	63.50[2.500]	60.96[2.400]	24	50	2-102540-3
OBSOLETE	60.96[2.400]	58.42[2.300]	23	48	2-102540-2
OBSOLETE	58.42[2.300]	55.88[2.200]	22	46	2-102540-1
OBSOLETE	55.88[2.200]	53.34[2.100]	21	44	2-102540-0
OBSOLETE	53.34[2.100]	50.80[2.000]	20	42	1-102540-9
OBSOLETE	50.80[2.000]	48.26[1.900]	19	40	1-102540-8
OBSOLETE	48.26[1.900]	45.72[1.800]	18	38	1-102540-7
OBSOLETE	45.72[1.800]	43.18[1.700]	17	36	1-102540-6
OBSOLETE	43.18[1.700]	40.64[1.600]	16	34	1-102540-5
OBSOLETE	40.64[1.600]	38.10[1.500]	15	32	1-102540-4
4 OBSOLETE	38.10[1.500]	35.56[1.400]	14	30	1-102540-3
4 OBSOLETE	35.56[1.400]	33.02[1.300]	13	28	1-102540-2
	33.02[1.300]	30.48[1.200]	12	26	1-102540-1
	30.48[1.200]	27.94[1.100]	11	24	1-102540-0
	27.94[1.100]	25.40[1.000]	10	22	1-102540-9
	25.40[1.000]	22.86[.900]	9	20	1-102540-8
4 OBSOLETE	22.86[.900]	20.32[.800]	8	18	1-102540-7
	20.32[.800]	17.78[.700]	7	16	1-102540-6
	17.78[.700]	15.24[.600]	6	14	1-102540-5
	15.24[.600]	12.70[.500]	5	12	1-102540-4
	12.70[.500]	10.16[.400]	4	10	1-102540-3
4 OBSOLETE	10.16[.400]	7.62[.300]	3	8	1-102540-2
	7.62[.300]	5.08[.200]	2	6	1-102540-1
	C MAX	B	A	REF. 1 NO OF POSN	PART NUMBER
COVER DIMENSIONS					

102540

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN RAGHAVENDRA

CHK JEFFREY GESFORD

APVD JEFFREY GESFORD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

06MAR09

06MAR09

06MAR09

—

—

—

SCALE 5:1

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, PA 17105-3608

COVER - HALF, LOW PROFILE

MASS TERMINATION AMPMODU,

.100CL, FULL BAR POLARIZATION

SIZE A2

CAGE CODE 00779

DRAWING NO C=102540

RESTRICTED TO

SHEET 1 OF 1

REV H1