





600 Series

Tubeaxial

60x60x25mm

- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics.
- With electronic protection against reverse polarity, blocking and overloading by PTC-resistor; partially impedance protected.
- Mounting from either face using four 3.7 mm holes.
- Fan of fiberglass reinforced plastic. PBTP housing, PA impeller.
- Air exhaust over struts. Rotational direction CW looking at rotor.
- Electrical connection via 2 leads AWG 22, TR 64. Stripped and tinned ends.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VDC	Volt. Range	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
605L	1	12	5	4.5 to 6	0.8	26	65	Ball	Leads	0.19
612GL	1	12	12	6 to 15	1.0	24	65	Sintec	Leads	0.19
612L	1	12	12	6 to 15	0.7	26	65	Ball	Leads	0.19
612GM	2	18	12	6 to 15	1.3	32	65	Sintec	Leads	0.19
612M	2	18	12	6 to 15	1.3	33	65	Ball	Leads	0.19
612	3	24	12	6 to 15	2.5	40	65	Ball	Leads	0.19
612G	3	24	12	6 to 15	2.8	40	65	Sintec	Leads	0.19
614GL	1	12	24	12 to 30	1.2	24	65	Sintec	Leads	0.19
614L	1	12	24	12 to 30	0.8	26	65	Ball	Leads	0.19
614M	3	18	24	12 to 30	1.4	33	65	Ball	Leads	0.19
614	3	24	24	12 to 30	2.5	40	65	Ball	Leads	0.19
614G	3	24	24	12 to 30	2.9	40	65	Sintec	Leads	0.19
614S	3	24	24	12 to 30	2.5	40	65	Ball	Leads	0.19
614H	4	27	24	12 to 27	3.4	44	65	Ball	Leads	0.19



ebmpapst

e-mail: sales@us.ebmpapst.com · TEL: 860-674-1515 · FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2004 © ebm-papst Inc. reserves the right to change any specifications or data without notice