



Sample photo

Order symbol: PC 100/35 LT
Product nbr: 6012901

Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN:	6418074022257
El. number:	
Finland	3420411
Denmark	8212022302
Italy	7352010
Sweden	2535603

Including: Base with TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:	130	80	35	Ingress Protection (EN 60529): IP 66/67	
inch:	5.1	3.1	1.4	Impact Resistance (EN 50102): IK 08	
Materials:					Electrical insulation: Totally insulated
Material:	PC				Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035				UV resistance: UL 508
Cover colour:	Smoked grey				Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:	Polyamide				Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Black				NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:	TPE				Certificates:
Temperatures:					Germanischer Lloyd (GL)
Short term:	-40 ... 120 °C				Underwriters Laboratories
Continuous:	-40 ... 80 °C				Det Norske Veritas
Short term:	-40 ... 250 °F				Fimko
Continuous:	-40 ... 175 °F				Europe EN 50298 1998
Accessories:					UL Canada
MIV 100	Mounting plate				Gost R
MIN 5	DIN-15 Mounting rail				
MIN 10	DIN-15 Mounting rail				
MIV 5	DIN-35 Mounting rail				
MIV 10	DIN-35 Mounting rail				
FP A 100/130	Front plate				
HFP 130	Front plate hinge series				

