





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECO-18-009360	15JUN2018	AP	DG

PART NUMBER	No. of Contact	A ± 0.20	B ± 0.20	C ± 0.20	D
2301844-1	09	16.34	24.99	30.81	11.08



P.C.B. LAYOUT

NOTE:

1. MATERIAL:

HOUSING: PBT WITH 20% GF UL 94 V-0, BLACK COLOR

CONTACTS: PHOSPHOR BRONZE.

SHELL:STEEL

GROUNDING BRACKET: BRASS

RIVETED INSERT: BRASS

SCREWLOCK: BRASS

2. FINISH:

CONTACTS: 0.36 μm [15 μ''] GOLD IN CONTACT AREA.

2.54 μm [100 μ''] MATTE TIN ON SOLDER TAILS

1.27 μm [50 μ''] NICKEL UNDERPLATE OVERALL

SHELL: 2.54 μm [100 μ''] NICKEL

RIVET: 1.27 μm [50 μ''] NICKEL

SCREWLOCK: 1.27 μm [50 μ''] NICKEL

BOARDLOCK: 1.27 μ m [50 μ "] MIN NICKEL UNDERPLATE.

2.54 μ m [100 μ "] MIN MATTE TIN PLATE

3. WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC.

109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN AJITH PAI 07FEB2017	TE Connectivity		
			CHK DAN GORENC 07FEB2017			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 07FEB2017	NAME		
	0 PLC ± -		PRODUCT SPEC	9 WAY D-SUB SOCKET WITH BOARD LOCK -		
	1 PLC ± 0.38		108-130013			
	2 PLC ± 0.25		APPLICATION SPEC			
	3 PLC ± 0.10		-	SIZE	CAGE CODE	DRAWING NO
	4 PLC ± -		WEIGHT	A2	00779	C-2301844
	ANGLES ± 2°		0	RESTRICTED TO		
MATERIAL	FINISH		CUSTOMER DRAWING	-		
-	-		SCALE 3:1			SHEET 1 of 4
						REV H

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PART NUMBER	No. of Contact	A ±0.20	B ±0.20	C ±0.20	D
2301844-2	09	16.34	24.99	30.81	11.08



P.C.B LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0	PLC	±	-
1	PLC	±	0.38
2	PLC	±	0.25
3	PLC	±	0.10
4	PLC	±	-
ANGLES		±	-

FINISH
-

DWN
AJITH PAI
07FEB2017

CHK
DAN GORENC
07FEB2017

APVD
-
07FEB2017

PRODUCT SPEC
108-130013

APPLICATION SPEC
-

WEIGHT
0

CUSTOMER DRAWING

DESCRIPTION
9W D SKT W B/L & 4-40 S/LOCK 15U" GOLD

TE PART NO
2301844-2

TE Connectivity

NAME
9 WAY D-SUB SOCKET WITH BOARD LOCK

SIZE A2	CAGE CODE 00779	DRAWING NO C=2301844	RESTRICTED TO -
------------	--------------------	-------------------------	--------------------

SCALE 3:1	SHEET 2 of 4	REV H
--------------	-----------------	----------



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D




C



DETAIL A

B



DETAIL A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 07FEB2017	 TE Connectivity					
DIMENSIONS: mm		CHK DAN GORENC 07FEB2017						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD — 07FEB2017		NAME 9 WAY D-SUB SOCKET WITH BOARD LOCK —			
	0 PLC ± — 1 PLC ± 0.38 2 PLC ± 0.25 3 PLC ± 0.10 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-130013					
	MATERIAL —		APPLICATION SPEC —		SIZE A2	CAGE CODE 00779	DRAWING NO C=2301844	RESTRICTED TO —
	FINISH —		WEIGHT 0		CUSTOMER DRAWING			
				SCALE 3:1	SHEET 3 of 4	REV H		


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



15.672	13.651	90	16	1440	2301844-2
13.080	11.059	90	16	1440	2301844-1
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 07FEB2017	 TE Connectivity		
DIMENSIONS: mm		CHK DAN GORENC 07FEB2017			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 9 WAY D-SUB SOCKET WITH BOARD LOCK —		
	0 PLC ± —				
	1 PLC ± 0.38				
	2 PLC ± 0.25				
	3 PLC ± 0.10				
	4 PLC ± —		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
	ANGLES ± —				
	—				
MATERIAL —	FINISH —	WEIGHT 0	A200779C=2301844—		
CUSTOMER DRAWING			SCALE 1:1	SHEET 4 of 4	REV H