




NOTE


1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

3 - TERMINAL SCREWS (2) AND WASHERS (2) FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 13-19 OZ	CONTACT ARRANGEMENT SPNO	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ----- 4 OZ MIN	L96 15A 125, 250 OR 480 VAC 1/8 HP 125 VAC, 1/4 HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC	ONE PLACE (.0) ± .030	
DIFFERENTIAL TRAVEL --- .0004 - .0025	L288 L299 L306	TWO PLACE (.00) ± .015	
OVERTRAVEL ----- .060 MIN	CE D A	THREE PLACE (.000) ± .005	
	16A 250V ~ T85 5E4	ANGLES ±	
		WEIGHT .078 LB	