

APart SDQ5P-BL ACTIVE SPEAKER

APart



The SDQ5P is a stereo loudspeaker set that consists of a passive loudspeaker and an active loudspeaker. The SDQ5P's easy set up makes it perfectly suited for Audio-visual applications (next to the projection screen or flat TV), monitoring or even for small presentations. Due to its stylish design, a seamless integration into every interior is assured.

The active loudspeaker is equipped with volume and tone controls, accurate clip indicators and a stereo 2 x 30 watts amplifier. This amplifier comes with High Quality balanced inputs, a stereo RCA Cinch input and a mini stereo jack input (PC, Mp3 player, ...). Both loudspeakers are magnetically shielded and offer an enhanced bass response by the DTB reflex tuning. The SDQ5P set comes with a 3m power cord and a loudspeaker cable (in white for the SDQ5P-W and black for the SDQ5P-BL) to link the active loudspeaker with the passive one. Each set is available in black or white.

As an option the SDQ5P loudspeaker set can be painted in any RAL colour (Ref; PAINT-CAB8). As each set consists of 2 loudspeakers you need to take the PAINT-CAB8 price into account for both loudspeakers. Please note that the minimum order quantity for the PAINT-CAB8 in this case is SDQ5P sets.

TECHNICAL SPECIFICATIONS

Type	Active 2-way HiFi Pro, DTB Reflex tuning
Cabinet	Enforced Poly Plastic
Woofer	5.25" HiFi PP Shielded
Tweeter	1" mylar shielded
Inputs	
RCA - Stereo Mini Jack	500 mV, 22 Kohm
Balanced Euroblock	500 mV, 22 Kohm
Tone Control	
Bass	± 12 dB at 80 Hz
Treble	± 12 dB at 12 kHz
RMS Power in 4 Ohm	
AES Rated	2 x 30 Watts
Dynamic PMPO	2 x 200 Watts
THD (Total Harmonic Distortion)	< 0.07%
Signal to Noise Ratio	> -90 dB
SPL 1 watt/1 m	91 dB
SPL Max peak	111 dB
Frequency Range	45Hz - 20 kHz
Dispersion	120°H x 100° V
IP rating	40
Dimensions (H x W x D) L & R speaker	238 x 181 x 170 mm (Bracket not included)
Weight	5.75 Kg, brackets included