








RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 50mA, @12V DC
5. TRAVEL: 0.30±0.15mm
- ▲ 6. OPERATING FORCE: 160±50gf
7. CONTACT RESISTANCE: 100 MILLIOHMS Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
9. ▲ DENOTES CRITICAL PARAMETER.

OBSOLETE

OCT. 2015

PCR 22014

E-SWITCH®

TITLE

TL1100BF160Q

SCALE

2:1

DATE

8/5/03

DR

AR

DWG

P001113

REV

A

A	13347	RELEASED FOR PRODUCTION	8/5/03	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED