




### FEATURES:

- Shielded cable to reduce noise
- Provides a quick connection between dual Bantam Jacks
- Dual Bantam Plugs are molded to the cable for optimum durability

### MATERIALS:

Plugs – Nickel plated brass

Cable – 4 Conductor shielded twisted pair, PVC jacket and insulation

### RATINGS:

Operating Temperature: -20°C to +80°C

Operating Voltage: 300 VRMS Max.

Current: 3.36 Amperes @ 25°C Max.

Nominal Capacitance Shield to Conductor: 250pf

Nominal Capacitance Between Conductors: 150pf

### ORDERING INFORMATION: Model 6331-96

Standard Length 96 Inches (2134 mm)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA